

# Eaton E34PB1-1X

Catalog Number: E34PB1-1X

Eaton, 30.5 mm Watertight/Oiltight Corrosion Resistant Pushbutton, Factory assembled, Black, Plastic Actuator, 1NO - 1NC, Non-illuminated, Flush mounting, NEMA 3, 3R, 4, 4X, 12, 13, Momentary, 30.5 mm, Flush Pushbutton, E34 Series

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton E34 pushbutton	E34PB1-1X
UPC	Product Length/Depth
782113704272	3.5 in
Product Height	Product Width
2 in	2.5 in
Product Weight	Warranty
0.2 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
FDA 3-A	CSA Certified

## defaultTaxonomyAttributeLabel

### Special features

Factory assembled

### Type

30.5 mm, Corrosion Resistant

### Actuator color

Black

### Bezel

Black

### Actuator material

Plastic

### Operating mode

Momentary

### Contact configuration

1 NO-1 NC

### Illumination

Non-illuminated

### Series

E34

### Mounting method

Flush

### Rating

NEMA 13

NEMA 4

NEMA 12

NEMA 4X

NEMA 3

NEMA 3R

### Degree of protection

NEMA 3R

NEMA 4

NEMA 4X

NEMA 3

NEMA 12

NEMA 13

### Product category

Flush pushbutton

### Size

## Resources

### Brochures

10250T and E34 Class I Division 2

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - E34PB1-1X

Cam selection for pushbutton selectors

30.5 mm

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)