

Eaton E49M11UP1

Catalog Number: E49M11UP1

Assembled Limit Switch, E49, Adjustable roller lever, Screw Terminals, 10A at 250 Vac, 1.5A at 24 Vdc, Standard DIN, 1 mm-2m/s, 1NO-1NC



General specifications

Product Name	Catalog Number
Eaton E49 compact metal limit switch	E49M11UP1
UPC	Product Length/Depth
782113680958	5.12 in
Product Height	Product Width
1.58 in	2.64 in
Product Weight	Warranty
0.58 lb	1 year

defaultTaxonomyAttributeLabel

Contact Rating

10A at 250 Vac, 1.5A at 24 Vdc

Enclosure material

Die cast aluminum

Actuator

Adjustable roller lever

Connection

Screw terminal

Contact configuration

1 NO-1 NC

Series

E49

Operating temperature - max

176 °F

Operating temperature - min

14 °F

Environmental rating

IP67

Maximum AC current

10 A continuous

Maximum DC current

1.5 A

Mounting method

Standard DIN rail

Operating speed

1 mm-2m/s

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E49M11UP1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)