



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E50KL539 E50 Operating Lever

Eaton Corp

Catalog Number	E50KL539
Manufacturer	Eaton Corp
Description	Limit Switch Lever, E50, Accessory, Adjustable Ball Bearing Roller, Used With Side Rotary, Stainless Steel
Weight per unit	0.1500 (lbs/each)
Product Category	Limit Switch Arms, Actuators &

### Features

actuator	Adjustable ball bearing roller
dimensions	4.6000 IN X 0.6900 IN X 0.8400 IN

### Descriptions

Description	E50 OPERATING LEVER
extra long description	ETN E50KL539 E50 OPERATING LEVER
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	Limit Switch Lever, E50, Accessory, Adjustable ball bearing roller, Used with side rotary, Stainless steel
Product Type	E50 Operating Lever

### Manufacturer Information

Brand	Eaton
GTIN	00782113361871
Manufacturers Part Number	E50KL539
UPC	782113361871

### Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch accessory

### Packaging

Carton	1
Weight Per each	0.15



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Ind Facilities & Factories - Industrial Facilities/Factories - Other .....
Operating Temperature .....	10 .....
standard .....	CE, CSA Certified, UL Listed, RoHS Compliant .....