

Eaton E50KL581

Catalog Number: E50KL581

Limit Switch Operator, E50, Accessory, Adjustable rod, 2.2 in-oz min. return, Used with side rotary, Metal

General specifications



Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch operator	E50KL581
	UPC
	782113308753
Product Length/Depth	Product Height
9.07 in	0.38 in
Product Width	Product Weight
1.12 in	0.3 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	
CE	

Type

Accessory

Used with

Used with side rotary

Actuator

Adjustable rod

Torque rating

2.2 in-oz min return

Series

E50

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental ratingNEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67**Material**

Metal

Catalogs[Eaton's Volume 8—Sensing Solutions](#)**Specifications and datasheets**[Eaton Specification Sheet - E50KL581](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)