



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **ECS98Y2CAJC1P7S3 Combo BRKR 250A 180A Nema 3R S611 480vac** *Eaton Corp*

Catalog Number	ECS98Y2CAJC1P7S3
Manufacturer	Eaton Corp
Description	Eaton S611 Soft Starter, Nema 3R, 200A/600V R Disconnect Fuse, Start/Stop, Hand-Off-Auto Selector SW, 250A Breaker, 180A, 460V
Weight per unit	250.0 (lbs/each)
Product Category	Soft Start Controllers & Start

### **Features**

Coil Voltage	120V/60 Hz
dimensions	61.7500 IN X 28.0000 IN X 10.6800 IN
media	Yes
Voltage Rating	460 V

### **Dimensions and Weight**

Size	180A max RVSS
------	---------------

### **Descriptions**

Description	COMBO BRKR 250A 180A NEMA 3R S611 480VAC
extra long description	ETN ECS98Y2CAJ-C1P7S3 Eaton S611 so
Features	The Eaton S611 is an innovative, economical soft starter combining advanced functionality, unsurpassed configuration flexibility, and an extremely comprehensive user interface. It is available in both open and enclosed control configurations to meet the needs of the commercial construction and OEM segment.
Long Description	Eaton S611 soft starter, NEMA 3R, 200A/600V R disconnect fuse, START/STOP, HAND-OFF-AUTO selector SW, 250A breaker, 180A, 460V
Product Type	Eaton S611 Soft Starter
Special Features	Standard size control power transformer

### **Manufacturer Information**

Brand	Eaton
GTIN	00786685620749
Manufacturers Part Number	ECS98Y2CAJ-C1P7S3
UPC	786685620749

### **Taxonomies, Classifications, and Categories**

Type	Soft starter
------	--------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	250

## Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	UL Listed,cUL Listed