



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EGB3040FFG E 3P 40A 18KA @ 415 & 480V Fixed Thermal Fixed Mag *Eaton Corp*

Catalog Number	EGB3040FFG
Manufacturer	Eaton Corp
Description	Eaton Series G Molded Case Circuit Breaker, Eg-Frame, Eg, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 40A, 600Y/347 Vac, 25 Kaic At 240 Vac, 18 Kaic At 480 Vac, Line and Load, 50/60 HZ
Weight per unit	2.9 (lbs/each)
Product Category	3 Pole

Features

Current Rating	40 A
dimensions	2.9900 IN X 3.0000 IN X 5.5000 IN
frame	EG
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600Y/347 Vac

Descriptions

Description	E 3P 40A 18KA @ 415 & 480V FIXED THERMAL FIXED MAG
extra long description	ETN EGB3040FFG E 3P 40A 18kA 415&48
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G molded case circuit breaker, EG-frame, EG, Complete breaker, Fixed thermal, fixed magnetic trip type, Three-pole, 40A, 600Y/347 Vac, 25 kAIC at 240 Vac, 18 kAIC at 480 Vac, Line and load, 50/60 Hz
Product Type	E 3P 40A 18KA 415&480V FXD Therm FXD Mag

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114876343
Manufacturers Part Number	EGB3040FFG
UPC	782114876343



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker

Packaging

Carton	1
Weight Per each	2.9

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
Frequency Rating	50/60 Hz
standard	CSA Certified, IEC Rated, UL Listed, CE Marked