



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EM3554T 1.5HP, 1770RPM, 3PH, 60HZ, 145T, 3524M, Tefc, F *Baldor/Abb Motors & Mechanical*

Catalog Number	EM3554T
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Baldor Electric; Ac Motor; Temperature Rating: 40 Deg C Amabient Condition; Horsepower: 1.5 HP; Phase: 3 PH; Voltage Rating: 230/460 Vac; Full Load Current: 4.5-4.4/2.2 Amp; Power Factor: 73; Service Factor: 1.15; Enclosure: Tefc; Frame: 145T; Insulation
Weight per unit	41.0 (lbs/each)
Product Category	Motors

Features

Base	Rigid
frame	145 W
horsepower	1.5 in in
Insulation Class	F
Phase	3 in
Power Factor	0.73 in
Service Factor	1.15 in
Speed Rating	1,760 rpm
Voltage Rating	208/230/460 V

Descriptions

Description	1.5HP,1770RPM,3PH,60HZ,145T,3524M,TEFC,F
extra long description	BALDOR EM3554T 1.5HP,1760RPM,3PH,60
Long Description	Baldor Electric; AC Motor; Temperature Rating: 40 DEG C Amabient Condition; Horsepower: 1.5 HP; Phase: 3 PH; Voltage Rating: 230/460 VAC; Full Load Current: 4.5-4.4/2.2 AMP; Power Factor: 73; Service Factor: 1.15; Enclosure: TEFC; Frame: 145T; Insulation
Product Type	1.5HP, 1760RPM, 3PH, 60HZ, 145T, 3526M, Tefc, F
Special Features	1.5HP,1760RPM,3PH,60HZ,145T,3526M,TEFC,F

Manufacturer Information

Brand	Baldor/Abb Motors & Mechanical
Manufacturers Part Number	EM3554T
sub brand	Super-E

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	41

Uses, Certifications, and Standards

Application	General Purpose
Enclosure	TEFC
Frequency Rating	60 Hz
Mounting	F1