



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EM3611T 3HP 1760RPM 3PH 60HZ 182T 3632M Tefc F1

Baldor/Abb Motors & Mechanical

Catalog Number	EM3611T
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Baldor Electric; Ac Motor; Temperature Rating: 40 Deg C Amambient Condition; Horsepower: 3 HP; Phase: 3 PH; Voltage Rating: 208-230/460 Vac; Full Load Current: 9-8.4/4.2 Amp; Power Factor: 75; Service Factor: 1.15; Enclosure: Tefc; Frame: 182T; Insulation
Weight per unit	73.0 (lbs/each)
Product Category	Motors

Features

Base	Rigid
frame	182 EA
horsepower	3 in
Insulation Class	F
Phase	3 in
Power Factor	0.75 in
Service Factor	1.15 in
Speed Rating	1,760 rpm
Voltage Rating	208/230/460 V

Descriptions

Description	3HP 1760RPM 3PH 60HZ 182T 3632M TEFC F1
extra long description	BALDOR EM3611T 3HP,1760RPM,3PH,60HZ
Long Description	Baldor Electric; AC Motor; Temperature Rating: 40 DEG C Amambient Condition; Horsepower: 3 HP; Phase: 3 PH; Voltage Rating: 208-230/460 VAC; Full Load Current: 9-8.4/4.2 AMP; Power Factor: 75; Service Factor: 1.15; Enclosure: TEFC; Frame: 182T; Insulation
Product Type	3HP, 1760RPM, 3PH, 60HZ, 182T, 3631M, Tefc, F1
Special Features	3HP,1760RPM,3PH,60HZ,182T,3631M,TEFC,F1

Manufacturer Information

Brand	BALDOR
GTIN	00781568138960
Manufacturers Part Number	EM3611T
sub brand	Super-E
UPC	781568138960

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	73

Uses, Certifications, and Standards

Application	General Purpose
Enclosure	TEFC
Frequency Rating	60 Hz
Mounting	F1