



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EM3710T 7 1/2HP 1770RPM 3PH 60HZ 213T 3738M Tefc F

Baldor/Abb Motors & Mechanical

Catalog Number	EM3710T
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Baldor Electric; Ac Motor; Phase: 3 PH; Voltage Rating: 230/460 Vac; Horsepower: 7.5 HP; Speed Rating: 1770 RPM; Frequency Rating: 60 HZ; Full Load Current: 18.8/9.4 Amp; Torque Rating: 22.4 LB-FT Full Load, 69.2 LB-FT Break Down, 36.1 LB-FT Pull-Up, 41.1
Weight per unit	184.0 (lbs/each)
Product Category	Motors

Features

Base	Rigid
frame	213 lm
horsepower	7.5 WO
Insulation Class	F
Phase	3 in
Power Factor	0.81 in
Service Factor	1.15 in
Speed Rating	1,770 rpm
Voltage Rating	230/460 V

Descriptions

Description	7 1/2HP 1770RPM 3PH 60HZ 213T 3738M TEFC F
extra long description	BALDOR EM3710T 7.5HP,1770RPM,3PH,60
Long Description	Baldor Electric; AC Motor; Phase: 3 PH; Voltage Rating: 230/460 VAC; Horsepower: 7.5 HP; Speed Rating: 1770 RPM; Frequency Rating: 60 HZ; Full Load Current: 18.8/9.4 AMP; Torque Rating: 22.4 LB-FT Full Load, 69.2 LB-FT Break Down, 36.1 LB-FT Pull-Up, 41.1
Product Type	7.5HP, 1770RPM, 3PH, 60HZ, 213T, 3736M, Tefc
Special Features	7.5HP,1770RPM,3PH,60HZ,213T,3736M,TEFC

Manufacturer Information

Brand	BALDOR
GTIN	00781568139042
Manufacturers Part Number	EM3710T
sub brand	Super-E
UPC	781568139042

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	184

Uses, Certifications, and Standards

Application	General Purpose
Enclosure	TEFC
Frequency Rating	60 Hz
Mounting	F1