

Eaton EMN25 D31 GSK M15

Catalog Number: EMN25 D31 GSK M15

Eaton Crouse-Hinds series EMN NEMA manual pushbutton starter, With starter, 7.5 HP/10 HP, Square D starter, Copper-free aluminum, NEMA size 1, Three-pole, Polyphase, 200-230 Vac/380-575 Vac, Gasket, M15 model



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EMN NEMA manual pushbutton starter	EMN25 D31 GSK M15
	UPC
	662276571143
Product Length/Depth	Product Height
7.94 in	10.44 in
Product Width	Product Weight
7.6 in	14.17 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

7

9

Product specifications

Enclosure

With starter

Manufacturer

Square D

Number Of Poles

Three-pole

NEMA size

1

Voltage rating

200-230 Vac/380-575 Vac

Phase

Poly-phase

Horsepower

7.5 hp/10 hp

Material

Copper-free aluminum

Special features

Gasket

Type

M15 model

Resources

Brochures

[EMN NEMA Pushbutton Style Explosionproof Motor Starters Brochure](#)

Catalogs

[EMN NEMA Pushbutton Style Explosionproof Motor Starters catalog page](#)

Certification reports

[EMN NEMA Pushbutton Style Explosionproof Motor Starters UL certification](#)

Installation instructions

[IF 1640 - EMN Series Pushbutton Line Starters and Enclosures](#)

[IF 1661 - EMN Series Replacement Pushbuttons](#)

Specifications and datasheets

[Eaton Specification Sheet - EMN25 D31 GSK M15](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)