Eaton ER53030UPGB

Catalog Number: ER53030UPGB

Eaton enclosed rotary disconnect switch, 30 A, Gray cover, black handle, NEMA 4X, Polycarbonate non-metallic, Max HP:7.5, 7.5, 15, 20 hp (@208,240,480,600 V), Three-pole, Product category: enclosed rotary non-fusible, R-Series, 600 V

General specifications

Product Name Catalog Number
Eaton enclosed rotary disconnect switch ER53030UPGB

UPC Product Length/Depth

786685403458 7 in

Product Height Product Width

5.5 in 5 in

Product Weight Warranty

1.5 lb Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications Catalog Notes

CSA Certified Gray Cover, Black Handle.

UL Listed



Physical Attributes

Color

Black handle

Gray cover

Enclosure

NEMA 4X

Enclosure material

Polycarbonate non-metallic

Handle color

Black

Number of poles

Three-pole

Series

R-Series

Type

Enclosed rotary disconnect

Performance Ratings

Amperage Rating

30A

HP rating - max

7.5, 7.5, 15, 20 hp (@208,240,480,600 V)

Voltage rating

600 V

Miscellaneous

Product Category

Enclosed rotary non-fusible

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Multimedia

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - ER53030UPGB

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia