# Eaton ER53030UPGR

# Catalog Number: ER53030UPGR

Eaton enclosed rotary disconnect switch, 30 A, Gray cover, red handle, NEMA 4X, Polycarbonate non-metallic, Max HP:7.5, 7.5, 15, 20 hp (@208,240,480,600 V), Three-pole, Product category: enclosed rotary non-fusible, R-Series, 600 V

## General specifications

Product Name Catalog Number
Eaton enclosed rotary disconnect switch ER53030UPGR

UPC Product Length/Depth

786685403465 7 in

Product Height Product Width

5.5 in 5 in

Product Weight Warranty

1.5 lb Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications Catalog Notes

UL Listed Gray Cover, Red Handle.

cUL Certified



# Physical Attributes

Color

Red handle

Gray cover

Enclosure

NEMA 4X

**Enclosure material** 

Polycarbonate non-metallic

Handle color

Red

Number of poles

Three-pole

Series

R-Series

Type

Enclosed rotary disconnect

## Performance Ratings

**Amperage Rating** 

30A

HP rating - max

7.5, 7.5, 15, 20 hp (@208,240,480,600 V)

Voltage rating

600 V

#### Miscellaneous

**Product Category** 

Enclosed rotary non-fusible

#### Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Multimedia

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - ER53030UPGR



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia