



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

425 East Germann Road Suite 101
85297-0000, AZ Gilbert
Phone: 602-325-9757
Fax: 602-325-9758



EREGYSLWPSQM12 Single Remote Head Grey Weatherproof

Lithonia Lighting - Acuity

Catalog Number	EREGYSLWPSQM12
Manufacturer	Lithonia Lighting - Acuity
Description	The Lithonia Lighting Gray Ere Led Remotes Are Suitable For Outdoor Lighting Applications, For Use As Part Of An Emergency Lighting System, Illuminating The Path Of Egress. These Single Led Lamp Remotes Are Fully Adjustable and Are Suitable For Wall or Ceiling Mounting.
Weight per unit	0.8600 (lbs/each)
Product Category	Emergency Lighting

Features

average life	100,000
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	45 LM
Material	Thermoplastic
Maximum Operating Temperature	50
Power Source	Hardwired
Shape	Square
Warranty	2

Material, Color, and Finish

Color	Gray
color temperature	6500
Finish	Textured
Lens Color	Clear
Lens Material	Plastic

Dimensions and Weight

Height	5
Length	7
Width	5.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

425 East Germann Road Suite 101
85297-0000, AZ Gilbert
Phone: 602-325-9757
Fax: 602-325-9758

Descriptions

Construction	New Construction,Remodel
Description	SINGLE REMOTE HEAD GREY WEATHERPROOF
extra long description	LITH ERE GY SGL WP SQ M12 Remote, G
Long Description	The Lithonia Lighting gray ERE LED Remotes are suitable for outdoor lighting applications, for use as part of an emergency lighting system, illuminating the path of egress. These single LED lamp remotes are fully adjustable and are suitable for wall or ceiling mounting.
Product Type	Remote Light Head

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00191848036785
Manufacturers Part Number	ERE GY SGL WP SQ M12
UPC	191848036785

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
----------------------	---------------------------

Packaging

Carton	1
Package	12
Weight	1
Weight Per each	0.86

Uses, Certifications, and Standards

Application	Education,Hospitality,Offices & Banks,Retail
environmental conditions	Indoor,Outdoor
Mounting	SURFACE
standard	C-UL-US,NFPA 101,NFPA 70,UL