


10316 - F30T8/CW 6PK

GE garage & basement 30 watt T8 1-pack

- · Ideal for utility use
- Lasts 3.4 years based on 6 hours per day usage
- 4100K cool white light appearance
- · Cool white light perfect for sizable spaces
- For use in large spaces such as basements and garages
- GE garage & basement fluorescent bulbs' cool white light is perfect for illuminating sizable spaces throughout your home. Use in large open spaces in your home including finished and unfinished basements, garages and rec
- 1.0 inch diameter T8 with medium bi-pin (g13) base
- 36 inches long





CAUTIONS & WARNINGS

Caution


- · Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- · Risk of Electric Shock
- Turn power off before inspection, installation or removal.
- *Three year life based on rated life at 6 hours/day.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution



Graphs_Lamp Mortality

GENERAL CHARACTERISTICS

Linear Fluorescent - Straight Lamp Type

Linear

Bulb

Medium Bi-Pin (G13) Base

Rated Life 7500.0 hrs **Bulb Material** Soda lime Starting Temperature (MIN) 10.0 °C

LEED-EB MR Credit 539 picograms Hg per mean

lumen hour

Primary Application Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens 2150.0 Mean Lumens 1980.0 Nominal Initial Lumens per Watt 71 Color Temperature 4100.0 K Color Rendering Index (CRI) 60.0

ELECTRICAL CHARACTERISTICS

Wattage 99.0 Voltage

Open Circuit Voltage 375 V @ 10 °C

(after preheating) Max @

Temperature

Cathode Resistance Ratio - Rh/ 4.25

Rc (MIN)

Cathode Resistance Ratio - Rh/ 6.5

Rc (MAX)

Open Circuit Voltage 176 V @ 10 °C

(after preheating) Min @

Temperature

Current Crest Factor (MAX) 1.7

DIMENSIONS

Maximum Overall Length 36.0000 in(914.4 mm)

(MOL)

Minimum Overall Length 35.6700 in(906.0 mm) Nominal Length 36.000 in(914.4 mm) Bulb Diameter (DIA) (MIN) 0.940 in(23.9 mm) Bulb Diameter (DIA) (MAX) 1.100 in(27.9 mm) Bulb Diameter (DIA) 1.000 in(25.4 mm)

35.220 in(894.6 mm) Max Base Face to Base Face (A)

Face to End of Opposing Pin

35.400 in(899.2 mm)

(B) (MIN)

Face to End of Opposing Pin 35.500 in(901.7 mm)

(B) (MAX)

End of Base Pin to End of 35.670 in(906.0 mm)

Opposite Pin End (C)

PRODUCT INFORMATION

Product Code 10316

Description F30T8/CW 6PK ANSI Code 2018-1 Standard Package **BUNDLE**

Standard Package GTIN 00043168103169

Standard Package Quantity 24 Sales Unit Unit No Of Items Per Sales Unit No Of Items Per Standard 24

Package

UPC 043168980524

