



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F44LE45A 4X4 45D N12 Top Open Elb

Hoffman Enclosures, Inc.

Catalog Number	F44LE45A
Manufacturer	Hoffman Enclosures, Inc.
Description	Elbow 45-Degree Top Opening, 4.00X4.00, Gray, Steel
Weight per unit	3.3 (lbs/each)
Product Category	20200714082358

Features

ip rating	IP54
Material	MILD STEEL

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

Dimensions and Weight

Height	4
Width	4

Descriptions

Description	4X4 45D N12 TOP OPEN ELB
extra long description	NVENT HOF F44LE45A 45 Elbow, top o
Features	Lay-in Hinged-Cover 45-Degree Elbows are used for continuous wireway runs with 45-degree turns. Because sections of lay-in wireway can be mounted with covers oriented in any direction, three different 45-degree elbows are available. Proper selection allows the user to maintain the same access and thereby preserve the lay-in feature for right-angle installations.
Long Description	Elbow 45-Degree Top Opening, 4.00x4.00, Gray, Steel
Product Type	45 Elbow, Top Open

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510183707
Manufacturers Part Number	F44LE45A
UPC	783510183707

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	ELBOW

Packaging

Carton	1
Weight Per each	3.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

nema rating

Power Distribution

12 Indoor, dust-resistant