



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F66L60 6X6X60" N12 Lay In STRT SCTN *Hoffman Enclosures, Inc.*

Catalog Number	F66L60
Manufacturer	Hoffman Enclosures, Inc.
Description	Straight Section Lay-In Hinged Cover Type 12, 6.00X6.00X60.00, Gray, Steel
Weight per unit	39.0 (lbs/each)
Product Category	20200715131805

Features

ip rating	IP54
Material	MILD STEEL

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

Dimensions and Weight

Height	6
Width	6

Descriptions

Description	6X6X60" N12 LAY IN STRT SCTN
extra long description	NVENT HOF F66L60 60.00in Straight S
Features	Lay-in NEMA Type 12 Wireway fittings are used primarily in industrial applications to protect wiring against exposure to oil and other contaminants. This gasketed wireway features quick-release latches for easy access and an opening on one side so wires and cables can be laid in along the entire run without pulling.
Long Description	Straight Section Lay-in Hinged Cover Type 12, 6.00x6.00x60.00, Gray, Steel
Product Type	60.00IN Straight Section

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510185305
Manufacturers Part Number	F66L60
UPC	783510185305

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Straight Section



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	39

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	12 Indoor, dust-resistant