Eaton FH85

Catalog Number: FH85

Eaton A200/B100 heater, Used with A200 Starter Sizes 3 and 4, 3PH Only, A200 Heater, NEMA, Ambient 67-73A, Non-Comp 62-67A, Used with A200 Starter Sizes 3 and 4, 3PH Only, Type A and B, Thermal and Fast Trip

General specifications



Product Name Eaton A200/B100 heater UPC 786678670997 Product Height 0.8 in Product Weight 0.05 lb Certifications CSA Certified UL Listed Catalog Number FH85 Product Length/Depth 2.1 in Product Width 1.3 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters



defaultTaxonomyAttributeLabel

Special features Used with A200 Starter Sizes 3 & 4, 3-Phase Only

Туре

A200 Heater

Used with

Used with A200 Starter Sizes 3 & 4, 3-Phase Only

Design

NEMA

Full load current range Ambient 67-73 A, Non-Comp 62-67 A

Overload relay

Type A and B

Trip type

Thermal and fast trip



Catalogs

Eaton's Volume 5—Motor Control and Protection

Installation instructions Instructions for A200, A210, A250 size 6, two- or three-pole nonreversing or reversing motor controllers

Specifications and datasheets Eaton Specification Sheet - FH85



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia