Product specifications

Eaton FNQ-R-1

Catalog Number: FNQ-R-1

Eaton Bussmann series FNQ-R fuse, 1 A, Class CC, Nonindicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V

General specifications

Product Name

Eaton Bussmann series FNQ-R fuse

UPC

051712147033

Product Height

0.41 in

Product Weight

0.15 lb

Compliances **CE Marked**

RoHS Compliant

Catalog Number

FNQ-R-1

Product Length/Depth

1.5 in

Product Width

0.41 in

Warranty

Not Applicable



Electrical Ratings

Amperage Rating

1 A

Voltage rating

600 V

General Information

Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Type

Current-limiting high inrush time-delay fuse

Resources

Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FNQ-R-1

Technical data sheets

FNQ-R-1~CLASS CC TIME DELAY

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia