

ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



FNQR25 25A 600V TD Class CC Fuse

Bussmann Fuses

Catalog Number	FNQR25
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNQ-R Fuse, 25 A, Class CC,
	Non-Indicating, Ferrule End X Ferrule End, 12 Sec At 200%, 200
	Kaic, Melamine Tube, Standard, 600 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

	25.4
amperage rating	25 A
class	Class CC
connection	Ferrule End X Ferrule End
dimensions	0.4100 IN X 0.4100 IN X 1.5000 IN
interrupt rating	200 kAIC
Material	Melamine Tube
media	Yes
Voltage Rating	600 V

Descriptions

Description	25A 600V TD CLASS CC FUSE
extra long description	EFSE FNQ-R-25 CLASS CC TIME DELAY R
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Long Description	Eaton Bussmann series FNQ-R fuse, 25 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V
Product Type	Class CC Time Delay Rejection Fuse

Manufacturer Information

Brand	Eaton
GTIN	00051712497138
Manufacturers Part Number	FNQ-R-25
UPC	051712497138



standard

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Taxonomies, Classifications, and Cate	gories
Category Description	MIDGET FUSES
Туре	FUSE
Packaging	
Carton	10
Weight Per each	0.02
Uses, Certifications, and Standards Application	Ind Facilities & Factories - Facility: Safety and Security Systems

CE Marked, RoHS Compliant