Eaton FNQ-R-3/4

Catalog Number: FNQ-R-3/4

Eaton Bussmann series FNQ-R fuse, 0.75 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAlC, Melamine tube, Standard, 600 V

General specifications



Eaton Bussmann series FNQ-R fuse

UPC

051712496933

Product Height

0.41 in

Product Weight

0.15 lb

Compliances

RoHS Compliant

CE Marked

Catalog Number

FNQ-R-3/4

Product Length/Depth

1.5 in

Product Width

0.41 in

Warranty

Not Applicable



Electrical Ratings

Amperage Rating

0.75 A

Voltage rating

600 V

General Information

Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Type

Current-limiting high inrush time-delay fuse

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FNQ-R-3/4

Technical data sheets

FNQ-R-3/4~FNQ-R-3-4~CLASS CC TIME DELAY



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia