

Eaton FNQ-R-5

Catalog Number: FNQ-R-5

Eaton Bussmann series FNQ-R fuse, 5 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V



General specifications

Product Name	Eaton Bussmann series FNQ-R fuse	Catalog Number	FNQ-R-5
UPC	051712147101	EAN	5027590060370
Product Length/Depth	0.41 in	Product Height	1.5 in
Product Width	0.41 in	Product Weight	0.15 lb
Warranty	Not Applicable	Compliances	CE Marked RoHS Compliant

Electrical Ratings

Amperage Rating

5 A

Voltage rating

600 V

General Information

Application

Line protection, small control transformers, industrial control, branch circuits

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Type

Current-limiting high inrush time-delay fuse

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FNQ-R-5](#)

Technical data sheets

[FNQ-R-5~CLASS CC TIME DELAY](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)