Eaton FRN-R-3-2/10

Catalog Number: FRN-R-3-2/10

Eaton Bussmann series FRN-R fuse, 3.2 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 8 sec at 500%, 200 kAIC at 250 V|20 kAIC at 125 Vdc, Standard, 250 V, 125 Vdc

General specifications



Eaton Bussmann series FRN-R fuse

UPC

051712507189

Product Height

0.81 in

Product Weight

0.1 lb

Compliances

CE Marked

Catalog Number

FRN-R-3-2/10

Product Length/Depth

3 in

Product Width

0.81 in

Warranty

Not Applicable



Electrical rating

Amperage Rating

3.2 A

Interrupt rating

20 kAIC at 125 Vdc 200 kAIC at 250 Vac

Response time

8 sec at 500%

Voltage rating

250 Vac, 125 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Finger safe

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FRN-R-3-2/10

Technical data sheets

FRN-R-3-2/10~FRN-R-3-2-10~FUSETRON DUAL-ELEMENT CLASS RK5



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia