

# Eaton FRN-R-4-1/2

Catalog Number: FRN-R-4-1/2

Eaton Bussmann series FRN-R fuse, 4.5 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 8 sec at 500%, 20 kAIC at 125 Vdc|200 kAIC at 250 V, Standard, 250 V, 125 Vdc



## General specifications

Product Name	Catalog Number
Eaton Bussmann series FRN-R fuse	FRN-R-4-1/2
UPC	EAN
051712507219	5027590426268
Product Length/Depth	Product Height
0.56 in	2 in
Product Width	Product Weight
0.56 in	0.5 lb
Warranty	Compliances
Not Applicable	CE Marked

## Electrical rating

### Amperage Rating

4.5A

### Interrupt rating

20 kAIC at 125 Vdc

200 kAIC at 250 Vac

### Response time

8 sec at 500%

### Voltage rating

250 Vac, 125 Vdc

## Physical details

### Number of elements

Dual

### Packaging type

Standard

## General information

### Class

Class RK5

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - FRN-R-4-1/2](#)

### Technical data sheets

[FRN-R-4-1/2~FRN-R-4-1-2~FUSETRON DUAL-ELEMENT CLASS RK5](#)