



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FT55DL841ECO Twin Fluor Lamp

Sylvania-Ledvance

Catalog Number	FT55DL841ECO
Manufacturer	Sylvania-Ledvance
Description	Dulux 55W Long Compact Fluorescent Lamp With 4 Pin Base, 4100K Color Temperature, 82 Cri, Ecologic For Use On Magnetic, Electronic and Dimming Ballasts
Weight per unit	0.4400 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

Features

amperage rating	Ballast Dependent
average life	12000
Ballast Type	Electronic and Dimming
Base	2G11
lumens	4800
Shape	T5
start type	Rapid & Instant Start, Preheat
total harmonic distortion	Ballast Dependent
Wattage	55

Material, Color, and Finish

color rendering index (cri)	82
color temperature	4100
Finish	Phosphor Coated

Dimensions and Weight

Diameter	0.625
Length	21.1

Descriptions

Description	TWIN FLUOR LAMP
extra long description	SYL FT55DL/841/ECO/20592 FT55DL841E
Long Description	DULUX 55W long compact fluorescent lamp with 4 pin base, 4100K color temperature, 82 CRI, ECOLOGIC for use on magnetic, electronic and dimming ballasts
Product Type	FT55DL841ECO 10/CS 1/Sku

Manufacturer Information

Brand	Sylvania (Usc)
GTIN	00046135205927
Manufacturers Part Number	FT55DL/841/ECO/20592
sub brand	Dulux L
UPC	046135205927



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Compact Fluorescent

Packaging

Carton	1
Package	10
Weight Per each	0.44

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------