

Eaton FWX-35A

Catalog Number: FWX-35A

Eaton Bussmann series FWX high speed fuse, 600V, 35A RMS, 200 kAIC Vac, 50 kAIC at 250 Vdc, Non Indicating, High speed fuse, Blade end X blade end, Stud

General specifications



Product Name	Catalog Number
Eaton Bussmann series FWX high speed fuse	FWX-35A
	UPC
	051712150477
Product Length/Depth	Product Height
3.44 in	0.89 in
Product Width	Product Weight
0.91 in	0.12 lb
Warranty	Compliances
Not Applicable	RoHS Compliant
	CE Marked
Certifications	
CSA Certified	
UL Recognized	

Electrical rating

Amperage Rating

35A RMS

Interrupt rating

50 kAIC at 250 Vdc

200 kAIC Vac

Voltage rating

600 V

Watt losses

4.2 W

Physical details

Packaging type

Standard

General information

Connection

Blade end x blade end

Fuse indicator

Non Indicating

Mounting method

Stud

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Specifications and datasheets

[Eaton Specification Sheet - FWX-35A](#)

Technical data sheets

[FWX-35A-BUSS HIGH SPEED FUSE](#)

[Bussmann series FWX 35-2500A high speed fuses data sheet no. 720005](#)

Technical service bulletins

[Datasheet - FNQ-30](#)