

Eaton GHB2025

Catalog Number: GHB2025

Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 25 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	GHB2025
	UPC
	786679172452

Product Length/Depth	Product Height
2.63 in	3 in

Product Width	Product Weight
2 in	1.21 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Federal Specifications Classification W- from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	C375B
	Certifications
	UL Listed

defaultTaxonomyAttributeLabel

Type

Molded case circuit breaker

Amperage Rating

25 A

Voltage rating

480Y/277 Vac, 125/250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

GHB

Circuit breaker frame type

Complete breaker

Series

Series C

Frame

G

Frequency rating

50/60 Hz

Interrupt rating

65 kAIC at 240 Vac

14 kAIC at 480Y/277 Vac

Number of poles

Two-pole

Resources

Application notes

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Motor protection circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[G-frame Molded Case Circuit Breaker Drawing](#)

Installation instructions

[Series C GB/GHB/GDB Circuit Breakers - IL](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C F-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - GHB2025](#)

[Series C G-Frame Time Current Curves](#)

Time/current curves

[Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)