

Specifications



Eaton GMA-1-R

GMA 1A BUSS fuse, 1-R

General specifications

PRODUCT NAME	Eaton Bussmann series GMA Fast-acting glass tube fuse
CATALOG NUMBER	GMA-1-R
UPC	051712647830
EAN	5027590501699
PRODUCT HEIGHT	20 mm
PRODUCT DIAMETER	5.2 mm
PRODUCT WEIGHT	0.7 g
WARRANTY	Not Applicable
COMPLIANCES	RoHS Compliant CE Marked

Product specifications

AMPERAGE RATING	1 A
INTERRUPT RATING	35 AIC at 250 Vac 10 kAIC at 125 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	60 min at 135%, 2 min at 200%
MATERIAL	Nickel-plated brass endcaps Glass tube
PACKAGING TYPE	Standard
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)
TYPE	Electronic- small dimension
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton GMA time delay glass tube fuses data sheet](#)

[Eaton Specification Sheet - GMA-1-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

