



SKU: GSW-110

UPC: 0032076021047

Features & Benefits:

Description: SPST Toggle Switch

Specs

Dimensions

Lead Length None

Additional Class Attributes

Control Style	Single Pole
Illuminated	No
Mounting Method	Recessed
Number of Positions	2
Speeds	1
Switch Outlet Grade	Commercial
Switch Style	Standard
Switch Type	Toggle
Warranty	1 Year
Wattage	5540

Material and Finish

Material Nickel

Additional Technical Specifications

Connector Amperage Rating CU (Derated where applicable)	20 Amps
Contact Arrangement	SPST
Contact Type	Maintained
Terminal Type	Screw and O-Ring

Testing Standards

Prop65 Compliance WARNING: Cancer and Reproductive Harm - www.P65warnings.ca.gov

Color

Color Chrome

Voltage

Maximum Voltage	277 V
Minimum Voltage	125 V

Environment and Temperature

Environmental Conditions	Indoor/Outdoor
---------------------------------	----------------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 5
UPC Code	03207602104