



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GT3MV 3 Lamp, 2'X4' Static Lensed Troffer, Electronic Ba *Lithonia Lighting*

Catalog Number	GT3MV
Manufacturer	Lithonia Lighting
Description	Lensed Troffer, T3 Bulb Shape, 48 In Length, 24 In Width, 3-1/8 In/7.9 CM Height, 120 to 277 V, 32 W, Electronic Ballast, Instant, White, 2850 LM Brightness (Lumens), Bi-Pin Base, 3 Lamps, 1 Ballasts, Steel Housing Material, Baked White Enamel, Recessed Mount, 12.4 LB/Ea
Weight per unit	20.0 (lbs/each)
Product Category	Fluorescent Recessed Architect

Features

average life	15,000
Hardware	Yes
Lamp Included	NO
Lamp Type	Fluorescent
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	3
pallet quantity	28
Shape	Rectangular
Warranty	2
Wattage	96

Material, Color, and Finish

Lens Color	Clear
Lens Material	Acrylic
Style	Traditional

Descriptions

Description	3 LAMP, 2'X4' STATIC LENSED TROFFER, ELECTRONIC BA
-------------	--

Manufacturer Information

GTIN	00745975081721
UPC	745975081721

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Troffer

Trade Size

aperture size	2x4
---------------	-----

Availability

Manufacturer Status	Inactive
---------------------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	20

Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	UL