

# Eaton GUAB26 SA

Catalog Number: GUAB26 SA

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 3" cover opening diameter, Copper-free aluminum, B shape, 3/4"



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover	GUAB26 SA
	<b>UPC</b>
	782274100265
<b>Product Length/Depth</b>	<b>Product Height</b>
3.5 in	4.38 in
<b>Product Width</b>	<b>Product Weight</b>
2 in	1.19 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

## Product specifications

### Shape

B

### Trade size

3/4"

### Cover opening diameter

3"

### Material

Copper-free aluminum

## Resources

### Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

### Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

### Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

### Specifications and datasheets

[Eaton Specification Sheet - GUAB26 SA](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)