

Eaton H1038

Catalog Number: H1038

Eaton Crouse-Hinds series throat bushing, Rigid/IMC, Insulated, Malleable iron, 150°C, Threaded, 3"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series throat bushing	H1038
	UPC
	784564112972
Product Length/Depth	Product Height
2.1 in	0.8 in
Product Width	Product Weight
1.1 in	0.02 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Conduit type

Rigid/IMC

Insulator

Insulated

Thread

Threaded

Trade size

3"

Material

Malleable iron

Temperature rating

150°C

Resources

Catalogs

[Crouse-Hinds series Insulating and Throat Bushings - Rigid-IMC catalog page](#)

Certification reports

[Insulating and Throat Bushings - Rigid-IMC Canadian certification](#)

[Insulating and Throat Bushings - Rigid-IMC UL certification](#)



Eaton Corporation plc

Eaton House

30 Pembroke Road

Dublin 4, Ireland

Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)