HALO

Description

Designed for sloped ceiling installations for ceilings from 2/12 to 6/12 pitch. The socket aiming mechanism allows the lamp to be aimed straight down in accordance with ceiling pitch (2/12 to 6/12). H47ICAT is designed for use in insulated ceilings where the housing will be in direct contact with insulation*. H47ICAT is Air-Tite gasketed to limit airflow between conditioned spaces and unconditioned areas.

Catalog #	Type
Project	
Comments	Date
Prepared by	

Specification Features

Housing

Aluminum double wall housing construction

Plaster Frame

Housing adjusts in plaster frame to accommodate up to 1" ceiling thickness. Galvanized steel construction. Plaster frame features include:

- Regressed locking screw for securing hanger bars
- Cutouts for easily crimping hanger bars in position
- Halo name embossed on plaster frame. The housing may be removed from plaster frame to provide access to the junction box
- Pre-installed Air-Tite ready ceiling contact gasket

Includes:

Bar Hangers

Got Nail!™

- Integral precisely positioned nail for engineered and natural framing
- Mini-foot leveling flange
- Integral T-Grid Clip, no accessory clips required

q-Channel bars with Pass-N-Thru™

- Unique inverted "q" interlocking channel for rigidity and stability
- Pass-N-Thru[™] feature allows bars to cross-over for tool-less shortening in tight spaces

Hinged junction box w/ Slide-N-Side™

- (3) Slide-N-Side™ Non-Metallic (NM) wire traps, allow wiring outside the hox
- For 14-2, 14-3, 12-2, 12-3 U.S. and 14-2, 14-3, 12-2 Canadian
- (4) 1/2" conduit pry-outs
- · Hinged door for easy access
- Box is repositionable 90° on frame to avoid obstructions

Quick Connect™

- (3) Push wire nuts included, for speed & reliability
- Clear caps for wire connection visibility

cULus Listed

- Compact 16 in³ volume
- Listed for max. (10) No. 12 AWG or (14) No. 14 AWG 90° C splice conductors in box

Air-Tite™ code compliant

- · Certified under ASTM E283
- Exclusive gasket seals aperture, frame & ceiling
- · No additional caulk required

Socket

- Porcelain socket with nickel plated brass screw shell
- Snap-in springs secure socket to socket plate, and may be detached when using socket supporting trims

 Exclusive socket aiming mechanism swivels and rotates to properly align lamp. Slope indicator provides quick and consistent lamp settings (factory set for 3/12 slope). Shipping insert protects socket from overspray.


Compliance

- cULus Listed 1598 Luminaire
- · cULus Listed Damp Location
- cULus Listed for Wet Location, covered ceiling, with select trims
- cULus Listed for feed through
- cULus Listed for direct contact with insulation and combustible material*
- Air-Tite code compliant. Certified under ASTM E283; not exceeding 2.0 cfm (0.944 L/s) air leakage rate tested at a 1.57 psf (75 Pa) pressure differential
- RoHS compliant
- *Not to be used in direct contact with spray foam insulation (Consult NEMA LSD57-2013)










H47ICAT

6" IC, Air-Tite, New Construction Slope Housing

FOR USE IN INSULATED CEILINGS

FOR DIRECT CONTACT WITH INSULATION*

Dimensions



Special Features

Got-Nail!™ bar hangers q-Channel bars with Pass-N-Thru™ Hinged J-Box with Slide-N-Side™ Quick Connect™ push wire nuts Air-Tite™ code compliant



Ordering Information

Sample Number: H47ICAT 498P

Order housing, trim and lamp (by others) separately for a complete luminaire.

H47ICAT = 6" insulated ceiling, airtight, slope ceiling recessed housing, new construction

Trims

Baffles



498 Coilex Baffle 90W PAR38 OD: 7-7/8" [200mm] 498P=Black Baffle, White Trim 498W=White Baffle, White Trim



496 Coilex Baffle with Reflector 75W A19, 100W R30, 85W BR30, 75W PAR30L OD: 7-7/8" [200mm] 496P=Black Baffle with Clear Reflector,

White Trim

496W=White Baffle with Clear Reflector, White Trim

<u>Adjustables</u>

78 Eyeball - 30° Tilt 65W BR30, 75W R30 0D: 8" [203mm] 78P=White 78PAT=White, Air-Tite 78SN=Satin Nickel 78TBZ=Tuscan Bronze

1417 Low Voltage Eyeball - 30° Tilt 20W 12V MR16 OD: 7-1/4" [184mm] 1417W=White Baffle, White Trim 1417P=Black Baffle, White Trim



170 Albalite Glass Lens with Reflector 60W A19 OD: 8" [203mm] 170P=Albalite Lens, White Trim 170PS=Albalite Lens, White Trim, Shower light

