DESCRIPTION

The H7UICAT housings is designed to be used in direct contact with insulation. The wide variety of trims available allows a number of different lighting effects to be created with one basic housing.

APPLICATION

The H7UICAT housings is suited for use in insulated ceilings in residential and commercial applications. The IC construction allows an unbroken insulation barrier to be maintained. AIR-TITE™ construction allows the housing to meet restricted airflow requirements.

Catalog #	Туре
Project	
Comments	
Prepared by	Date

DESIGN FEATURES

A...Housing

Double wall aluminum construction for greater heat dissipation.

B...Socket Plate

Fixed socket plate maintains consistent lamp position.

C.-Plaster Frame

Housing adjusts in plaster frame 1 3/8" to accommodate different ceiling thicknesses. Plaster frame features include:

- · Regressed locking screw for securing hanger bars
- Cutouts for easily crimping hanger bars in position
- · Halo name embossed on plaster frame Galvanized steel construction. The housing can be removed from plaster frame to provide access to the junction box.

D...Junction Box

Junction box features include:

- UL listed for through branch circuit wiring
- Positioned to accommodate straight conduit runs
- Seven 1/2" trade size conduit knockouts with true pry-out slots
- Slide-N-Side™ connectors

allow 14/2 or 12/2 non-metallic sheathed cable to be installed without tools and without removing knockouts

E…GOT NAIL! Pass-N-Thru™ Bar Hangers

Bar Hanger Features include:

- Pre-installed nail easily installs in regular lumber, engineered lumber and laminated beams
- Safety and guidance system prevents snagging, ensures smooth straight nail penetration and allows bar hangers to be easily removed if necessary.
- Automatic levelling flange aligns the housing and lets you hold the housing in place with one hand while driving nails
- Housing can be positioned at any point within 24" joist span
- Score lines allow "tooless" shortening for 12" joists
- Bar hangers may be repositioned 90°
- Bar hangers do not need to be removed from frame for shortening
- Integral T-bar clips snaps onto T-bars - no additional clips required

F...Socket

Porcelain socket with nickel plated brass screw shell, snaps into trim for consistent lamp positioning.

G.-Thermal Protector

Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping.

Labels

- UL Listed for Damp Location
- UL listed for Feed Through
- UL listed for Direct Contact with Insulation and combustible material
- CSA Certified

Meets following requirements:

- State of California Title 24
- Washington State Energy Code
- International Energy Conservation Code (IECC)
- New York State Energy **Conservation Construction** Code
- Certified Under ASTM-E283



H7UICAT

6" Insulated Ceiling **Recessed Housing**

6" TRIMS

FOR USE IN INSULATED CEILINGS

FOR DIRECT CONTACT WITH INSULATION



with all trims listed



UPGRADE FEATURES:

- SLIDE-N-SIDE™ JUNCTION BOX
- GOT NAIL!™ BAR HANGERS
- PASS-N-THRU™ BAR HANGERS REGRESSED LOCKING SCREW
- HALO ID ON PLASTER FRAME

7 1/4" [184mm] Top View [228mm] 0 6 1/2" [165mm] 10 1/2" [267mm]

Ordering information on reverse

ADV042496 Supersedes ADV023111 & ADV000306 TAB: Recessed Incandescent

ORDERING INFORMATION


SAMPLE NUMBER: H7UICT-426RG

Order housing, trim and accessories separately.

Housing

Trims

H7UICAT=7" Insulated Ceiling AIR-TITE Housing





77P=White Eveball

8" (203mm)

75

172

Shower Light

75W A19, 75W PAR30 172PS=Shower Light OD: 7 3/4" (197mm)

Note: Specifications and Dimensions subject to change without notice.