

Eaton HCTR6

Catalog Number: HCTR6

Eaton Edison HCTR fuse, Current-limiting high inrush, Rejection style, 6 A, Class CC, Non-indicating, 12 sec at 200%, 200 kAIC, Nickel-plated brass endcaps|Melamine tube, Standard, 10, 600 V

General specifications

Product Name	Catalog Number
Eaton Edison HCTR fuse	HCTR6
UPC	Product Length/Depth
782634802242	1 in
Product Height	Product Width
0.406 in	0.406 in
Product Weight	Warranty
0.1 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	



Electrical rating

Amperage Rating

6 A

Interrupt rating

200 kAIC

Response time

12 sec at 200%

Voltage rating

600 V

Physical details

Material

Melamine tube

Nickel-plated brass endcaps

Packaging type

Standard

General information

Class

Class CC

Fuse indicator

Non-indicating

Quantity

10

Special features

Rejection style

Resources

Catalogs

[Edison full line catalog 1005](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - HCTR6](#)