



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

132 Professional Dr.  
72023-0000, AR Cabot  
Phone: 501-605-1780  
Fax: 501-605-1785



## HJ1614HWPL2LG 15.8X13.8X6 N4X FG FLT HC

Hoffman Enclosures, Inc.

Catalog Number	HJ1614HWPL2LG
Manufacturer	Hoffman Enclosures, Inc.
Description	Flat Cover With Latches Type 4X, 15.81X13.81X5.99, LT Gray, Fiberglass
Weight per unit	10.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

### Features

ip rating	IP66
Material	Fiberglass

### Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte
Style	No Window

### Dimensions and Weight

Depth	5.99
Height	15.81
Size	17.31x15.30x6.70 in
Width	13.81

### Descriptions

Description	15.8X13.8X6 N4X FG FLT HC
extra long description	NVENT HOF HJ1614HWPL2LG TYPE 4X, FL
Features	Enclosures feature a flat, overlapping cover design that ensures a more-secure seal. Available with solid and window covers. Latches provide easy access and security.
Long Description	Flat Cover with Latches Type 4X, 15.81x13.81x5.99, Lt Gray, Fiberglass
Product Type	Type 4X, Flat HNG Latch CVR
Short Description	TYPE 4X, FLAT HNG LATCH CVR

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510158910
Manufacturers Part Number	HJ1614HWPL2LG
UPC	783510158910

### Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

132 Professional Dr.  
72023-0000, AR Cabot  
Phone: 501-605-1780  
Fax: 501-605-1785

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
--------	---

Weight Per each	10
-----------------	----

## Uses, Certifications, and Standards

Application	Corrosive Environments, Controls and Drives
-------------	---

nema rating	4X Watertight, corrosion-resistant
-------------	------------------------------------