



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1300 Hwy 34 South
75160-0000, TX Terrell
Phone: 972-563-2224
Fax: 972-563-2227



HLBC6LS9FSE010 6" Led Slim DWNLT CCT Canless or Retrofit 120/277V

Cooper Lighting Solutions

Catalog Number	HLBC6LS9FSE010
Manufacturer	Cooper Lighting Solutions
Description	6" Downlight, 900/1100 Selectable Lumens, 90 Cri Selectable CCT D2W Option 120/277V 60HZ, 0-10V Dimmable Matte White Flange Canless or Retrofit Installation Compliant All States But Ca
Weight per unit	2.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.059A at 277V
Lamp Type	LED
Voltage Rating	120/277V
Wattage	16.5 W

Material, Color, and Finish

Finish	Matte White
Style	(blank)

Descriptions

Description	6" LED SLIM DWNLT CCT CANLESS OR RETROFIT 120/277V
extra long description	CLS HLBC6LS9FSD2WE010MWR 6" HLBC, L
Long Description	6" downlight, 900/1100 selectable lumens, 90 CRI selectable CCT D2W option 120/277V 60Hz, 0-10V dimmable matte white flange canless or retrofit installation compliant all states but CA
Product Type	6" HLBC, LS, 5CCT, D2W, 0-10V, Retrofit
Special Features	Available in 4" and 6"

Manufacturer Information

Brand	HALO
GTIN	00080083263257
Manufacturers Part Number	HLBC6LS9FSD2WE010MWR
UPC	080083263257

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	HLBC Slim Regressed Canless Downlight

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	2.03



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1300 Hwy 34 South
75160-0000, TX Terrell
Phone: 972-563-2224
Fax: 972-563-2227

Uses, Certifications, and Standards

Application	lighting
Mounting	CEILING
standard	Energy Star Certified;IECC Compliant;Title 20 Compliant;Title 24 Compliant;UL Listed;RoHS Compliant