COOPER Bussmann

In-line Fuse Holders for ¹/₄" x ¹/₈" to 1¹/₄" Fuses

HFB & HFB-10



Specifications Description: Waterproof in-line fuse holder for ¼" x 1¼" fuses.

Dimensions: See Dimensions illustration.

Construction: Thermoplastic rubber body with tin-plated, copper contacts. Ratings:

Volts: - 32V

Amps: - 30A max

Catalog Numbers

Catalog

Numbers	Description		
HFB*	Standard Pack (10-in)		
BK/HFB	Bulk Pack (100-in)		
BK/1A2294	HFB Replacement Contact Clip		
1A2294-01	HFB-10** Replacement Contact Clip		

*HFB accepts #12 to #18 wire leads (not provided). See Data Sheet for recommended crimp tools.

**HFB-10 accepts #10 wire leads (not provided). See Data Sheet for recommended crimp tools


Features/Benefits

- · Simple assembly with one-piece thermoplastic (important information molded into body)
- · High visibility yellow color for easy identification in dark or hard-to-access locations
- · Ideal for shock and vibration environments; withstands many organic solvents; temperature range -40/+150°C

Typical Applications

· Supplemental, Low Voltage, Low Amperage Control Circuits





Data Sheet: 2102



Specifications

Description: Universal in-line fuse holder for $\frac{1}{4}$ x $\frac{7}{6}$, 1" and 1 $\frac{1}{4}$ " fuses. Dimensions: See Dimensions

illustration.

Construction: Nylon body with tinplated, copper contacts.

Ratings:

- Volts: 32V
- Amps: 30A max

Flammability Rating: UL 94V2.

Pull Force: 5lbs minimum to separate

fuse holder housing with fuse installed.

Features and Benefits

 HHB Universal in-line fuse holder for 1/4" x %", 1" and 1 1/4" fuses.

Typical Applications


· Supplemental, Low Voltage, Low Amperage Control Circuits

Catalog Numbers

Holder - with	nout leads* - RoH	S compliant			
Catalog Numbe					
HHB-R	Standard Pack (10-in)				
BK/HHB-R	Bulk Pack (100-in)				
*Accepts #12 to #1	16 wire leads (not provi	ded with basic fuse			
holder). See Data	Sheet for recommende	d crimp tools.			
Holder - with	pre-attached #1	4 Insulated			
lead wires - N	ot RoHS complia	nt unless			
noted					
Catalog Numbe	Wire				
19" Length	8" Length	Color			

19" Length	8" Length	Color
BK/HHB-Y419	BK/HHB-Y408	Yellow
BK/HHB-R419	BK/HHB-R408**	Red
BK/HHB-B419	BK/HHB-B408	Black
**RoHS compliant.		

Dimensions - in (mm) Fuse Holder Length "L" **Fuse Length** %" (AGW) 2.100 Max



HRK



Specifications Description: Universal in-line fuse holder for 1/4" x 7/8" to 1 1/4" fuses.

Dimensions: See Dimensions illustration.

Construction: 8" (203mm) #14 lead wires.

Ratings:

Volts: - 32V

Amps: - 15A max

Features and Benefits

· HRK Universal in-line fuse holder for 1/4" x 1/6", 1" and 11/4" fuses with #14 lead wires.

· RoHS compliant

Typical Applications


· Supplemental, Low Voltage, Low **Amperage Control Circuits**

Catalog Number

Catalog Number	Amp	Valla	Euro Description		
Number	Rating	VOIts	Fuse Description		
HRK-R*	15	32	¼" diameter fuses of		
			different lengths.		
*Three springs furnished with fuse holder to accommodate					

different length 1/4" fuses.

Dimensions - in (mm)



Data Sheet: 2103

Data Sheet: 2111

For product data sheets, visit www.cooperbussmann.com/datasheets/ulcsa