



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC22W 6" Ic Rated Recessed Can W/Wago Clip *Lithonia Lighting*

Catalog Number	IC22W
Manufacturer	Lithonia Lighting
Description	Incandescent Airtight Housing, Round, 90 W, Galvanized, Steel Fixture Material, Aluminum Housing Material, Non Dimmable, 6 In Aperture Size, 19 LB
Weight per unit	4.0 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
media	Yes
Number of Lamps	1
Shape	Round

Dimensions and Weight

Height	7.75
Length	13.5
Width	17.5

Descriptions

Construction	New Construction
Description	6" IC RATED RECESSED CAN W/WAGO CLIP
extra long description	LITH IC22 W 6IN Incandescent New Co

Manufacturer Information

Brand	JUNO
GTIN	00661209067739
Manufacturers Part Number	IC22 W
UPC	661209067739

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	Housing

Packaging

Carton	1
Package	6
Weight Per each	4

Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	CSA,UL