



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

K2C17B1  
 7818102569544  
 10-7 STR 7/8 POST 2 COND  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Stud Length (in)	7/8,0.87
Thread Size	1/4-20
Height (in)	0.84
D or Diameter (Fraction) (in)	1
Nut Width (Fraction)	5/8
Nut Width (in)	0.62
D - in	1.00
Body Width (Fraction)	7/16
Body Width (in)	0.44
Height (Fraction) (in)	7/8

**General**

**Product Description**  
 Mechanical Grounding Connector,  
 2 Cables to Flat, 10 - 7 AWG (Str)  
 / 10 - 6 AWG (Sol), 1/4" Stud

**Conductor(s)**

Copper Solid Size (Range)	10 AWG-6 AWG
Copper Stranded (Range)	10 AWG-7 AWG

**Physical**

Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Leaded Bronze Alloy

**Approvals / Certifications**

Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL467

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175