



KA4C

by Burndy
Catalog ID: KA4C

Prop 65 Notice

Copper Terminal, 1 Hole, 14 AWG (Sol)-4 AWG (Str), 1/4" Stud, 1 Screw.

Features: Compact, Economical, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks,
Dimension N: 1/4 IN, Dimension K: 9/32 IN, Dimension T: 7/64 IN, Tongue Width: 9/16 IN, Installation Torque: 45 IN-LB, Stud/bolt Hole Size: 1/4 IN, Length: 1-1/8 IN, Height: 3/4 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks
Connector Type	Terminal
Hardware Type	5 / 16 "
Installation Torque Recommended in-lb	45 LBS/in
Material	Copper
Material - Hardware	Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	KA-LUG
Type	Bolted Lugs & Terminals
UPC	781810361405

Dimensions

Dimension - B Length fraction	8/17 in
Dimension - B Length inch	0.47 in
Dimension - Height fraction	3/4
Dimension - Height inch	0.77 in
Dimension - Hole Size fraction	9/32
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.11 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.54 in
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)