



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## KS27 Servit 1 STR - 3/0 STR *Burndy LLC*

Catalog Number	KS27
Manufacturer	Burndy LLC
Description	Copper Split Bolt, Cu: 1 Awg-3/0 Awg (STR) (Run & Tap).
Weight per unit	0.2160 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
pallet quantity	8700

### Descriptions

Description	SERVIT 1 STR - 3/0 STR
extra long description	BUR KS27 SERVIT 1 STR - 3/0 STR
Long Description	Copper Split Bolt, Cu: 1 AWG-3/0 AWG (Str) (Run & Tap).
Product Type	Mechanical
Special Features	Features: Compact, High Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Season Cracking And Corrosion, The SERVIT Provides Maximum Pressure And Assures A Secure Connection On All Combinations Of Run And Tap Conductors, Conductor Type: Run: Commercial Stranded And Solid Copper, Tap: Commercial Stranded And Solid Copper, Installation Torque: 500 IN-LB, Width: 1.17 IN, Cross Flats: 1.36 IN, Length: 1.86 IN

### Manufacturer Information

Brand	BURNDY
GTIN	00781810013557
Manufacturers Part Number	KS27
sub brand	SERVIT
UPC	781810013557

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KS

### Packaging

Carton	1
Package	25
Weight Per each	0.216

### Uses, Certifications, and Standards

Application	For Direct Burial Cables
standard	UL 486A;UL486B