



# KSU23, Split Bolt Connector with Spacer, Tin Plated

By Burndy  
Catalog # [KSU23](#)

Tin-plated, high strength copper alloy SERVIT with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors, 1.48 IN L.



## Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel

## General

EU RoHS Indicator	Yes
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL SERVIT
Trade Name	SERVIT®
Type	KSU, Universal
UPC	781810036006

## Dimensions

Dimension - Length Overall inch	1.56
Width	0.59 in

## Conductor Related

Conductor - ACSR Str Run Range	3 AWG - 2 AWG
Conductor - ACSR Str Tap Range	6 AWG - 2 AWG
Conductor - AL Str Run Range	8 AWG - 2 AWG
Conductor - AL Str Tap Range	8 AWG - 2 AWG
Conductor - Copper Str Run Range	8 AWG - 2 AWG
Conductor - Copper Str Tap Range	8 AWG - 2 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	17400

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..041343-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-KSU23-SPEC-EN | REV 8/2023