

Eaton KTS-R-10

Catalog Number: KTS-R-10

Eaton Bussmann series KTS-R fuse, 70/30 brass end cap, Panelboards, 10 A, 1, Class RK1, Non-indicating, Ferrule end x ferrule end, 200 kAIC at 600 Vac, Melamine glass tube, Standard, 600 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series KTS-R fuse	KTS-R-10
UPC	EAN
051712417037	5027590446303
Product Length/Depth	Product Height
0.8 in	5 in
Product Width	Product Weight
0.8 in	0.13 lb
Warranty	Compliances
Not Applicable	CE Marked

Electrical rating

Amperage Rating

10 A

Interrupt rating

200 kAIC at 600 Vac

Voltage rating

600 V

Physical details

Material

Melamine glass tube

Number of elements

1

Packaging type

Standard

General information

Class

Class RK1

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

70/30 brass end cap

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - KTS-R-10](#)

Technical data sheets

[KTS-R-10-LIMITRON FAST ACTING FUSE CLASS RK1](#)

[Bussmann series KTS-R 600 V Class RK1 fuse data sheet no. 1044](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)