

Eaton L1430P

Catalog Number: L1430P

Eaton locking plug, #16-12 AWG, 30A, Industrial, 125/250V, Back wiring, Black, white, Ultra grip, L14-30, Three-pole, Four-wire, Nylon



General specifications

Product Name	Catalog Number
Eaton Arrow Hart standard locking plug	L1430P
UPC	Product Length/Depth
032664544859	1.74 in
Product Height	Product Width
3.52 in	1.81 in
Product Weight	Compliances
0.24 lb	Federal Specifications Classification W-C375
	RoHS Compliant
Certifications	
CSA certified	
UL Listed	
NOM	

Product specifications

Special features

Severe duty locking connector

Color

Black

White

Face/body material

Thermoplastic

Wiring method

Back

Material

Thermoplastic

Allowable wire size

#16-12 AWG

Amperage Rating

30A

Number Of Poles

Three-pole

Contact material

Brass

Type

Locking plug

Device grade

Commercial

NEMA configuration

L14-30

Design type

Standard locking plug

Number of wires

4

Grounding

Operating temperature

-20 to 60 °C (-4 to 140 °F)

Voltage rating

125/250 V

Cord diameter

0.25-0.69 in (6.4 mm-17.5 mm)

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - L1430P](#)

Application

Industrial

Torque rating

20 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)