



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

411 Autumn Street
71901-0000, AR Hot Springs
Phone: 501-762-8210
Fax: 501-762-8211



L1530CW Conn WT 30A 250V 3PH 3P4W H/L YI *Eaton Wiring Devices*

Catalog Number	L1530CW
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Watertight Locking Connector, #18-10 Awg, 30A, Industrial, 250V, Back Wiring, Yellow, Steel, Watertight, L15-30, Three-Pole, Four-Wire, Santoprene Thermoplastic Elastomeric, 0.43 to 1.15 In, Ip67
Weight per unit	10.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

dimensions	6.7500 IN X 4.2500 IN X 3.7500 IN
media	Yes

Descriptions

Description	CONN WT 30A 250V 3PH 3P4W H/L YL
extra long description	EWD L1530CW Conn WT 30A 250V 3PH 3P
Features	Eaton's Arrow Hart watertight locking devices utilize a unique, robust design and superior materials to provide watertight security in harsh environments.
Long Description	Eaton Arrow Hart watertight locking connector, #18-10 AWG, 30A, Industrial, 250V, Back wiring, Yellow, Steel, Watertight, L15-30, Three-pole, Four-wire, Santoprene thermoplastic elastomeric, 0.43 to 1.15 in, IP67
Product Type	Conn WT 30A 250V 3PH 3P4W H/L YI
Special Features	Watertight locking

Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00040893642116
Manufacturers Part Number	L1530CW
UPC	040893642116

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Watertight

Packaging

Carton	1
Package	10
Weight Per each	10



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

411 Autumn Street
71901-0000, AR Hot Springs
Phone: 501-762-8210
Fax: 501-762-8211

Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Facility - OtherCommercial /
Institutional Buildings / Structures - Commercial / Institutional
Buildings / Structures - Other

standard

NOM,UL Listed,CSA certified,cULus Listed,Federal Specifications
Classification W-C375,RoHS Compliant