FEATURES:

Material: Tin Plated CU

UL listed for U.S. & Canada.

- Wire connector rated for 35Kv max.
 Class B/C compressed, concentric, and compact copper conductor
- Expanded wire range when installed with dieless NSi compression tool (N12ID).
- Dimensions are for referene only.


L Series: L256


POLARIS


PROGRAM: SOLIDWORKS **UPDATED:** 4/2022

SALES REV: A

SIZE: B (11x17)







+			COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS)										
			NSI			GREENLEE	ILSCO		BURNDY	T&B	HUSKIE		
WIRE SIZE	STRIP LENGTH	DIE COLOR	EXPANDED WIRE RANGE W/N12ID	N1240 SERIES	NSI-12	NSI-12	1240 SERIES	ILC-12/ILC-15 SERIES		Y-35, Y750, PAT 750 TBM-15, TBM-14M		EP510C	
#2AWG	1-3/16"	BROWN	#2AWG-#6AWG	KC12-2 (2)	CD4 (4)	HT41AW (4)	KC12-2 (2)	ILD-4 (4)	KC12-2(2)	U2CRT (2)	15528 (4)	HT41AW (4)	CD4 (4)

