



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L3504 Baldor Electric; Ac Motor; Temperature Rating: 40

Baldor/Abb Motors & Mechanical

Catalog Number	L3504
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Baldor Electric; Ac Motor; Temperature Rating: 40 Deg C Amambient Condition; Phase: 1 PH; Voltage Rating: 115/230 Vac; Service Factor: 1.25; Enclosure: Tefc; Frame: 56; Insulation Class: B; Horsepower: 0.5 HP; Speed Rating: 1725 RPM; Frequency Rating: 60 H
Weight per unit	27.0 (lbs/each)
Product Category	Motors

Features

Base	Rigid
frame	56 V
horsepower	0.5 in
Insulation Class	F
Phase	1 PH
Power Factor	0.66 LB
Service Factor	1.25 IN
Speed Rating	1,725 rpm
Voltage Rating	115/230 VAC

Descriptions

Description	BALDOR ELECTRIC; AC MOTOR; TEMPERATURE RATING: 40
extra long description	BALDOR L3504 .5HP,1725RPM,1PH,60HZ,
Long Description	Baldor Electric; AC Motor; Temperature Rating: 40 DEG C Amambient Condition; Phase: 1 PH; Voltage Rating: 115/230 VAC; Service Factor: 1.25; Enclosure: TEFC; Frame: 56; Insulation Class: B; Horsepower: 0.5 HP; Speed Rating: 1725 RPM; Frequency Rating: 60 H
Product Type	.5HP, 1725RPM, 1PH, 60HZ, 56, 3421L, Tefc, F1
Special Features	.5HP,1725RPM,1PH,60HZ,56,3421L,TEFC,F1

Manufacturer Information

Brand	Baldor/Abb Motors & Mechanical
Manufacturers Part Number	L3504

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors

Packaging

Carton	1
Weight Per each	27



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application.....	General Purpose.....
Enclosure.....	TEFC.....
Frequency Rating.....	60 Hz.....
Mounting.....	F1.....