

# Eaton L630P

Catalog Number: L630P

Eaton locking plug, #16-12 AWG, 30A, Industrial, 250V, Back wiring, Black, white, Ultra grip, L6-30, Two-pole, Three-wire, Nylon



## General specifications

Product Name	Catalog Number
Eaton Arrow Hart standard locking plug	L630P
UPC	Product Length/Depth
032664393501	2.02 in
Product Height	Product Width
3.79 in	2.02 in
Product Weight	Compliances
0.23 lb	Federal Specifications Classification W-C375
	RoHS Compliant

## Certifications

UL Listed  
NOM  
CSA certified

## Product specifications

### Special features

Severe duty locking connector

### Color

White

Black

### Face/body material

Thermoplastic

### Wiring method

Back

### Material

Thermoplastic

### Allowable wire size

#16-12 AWG

### Amperage Rating

30A

### Number Of Poles

Two-pole

### Contact material

Brass

### Type

Locking plug

### Device grade

Commercial

### NEMA configuration

L6-30

### Design type

Standard locking plug

### Number of wires

Grounding

3

### Operating temperature

-20 to 60 °C (-4 to 140 °F)

### Voltage rating

250 V

### Cord diameter

0.25-0.69 in (6.4 mm-17.5 mm)

## Resources

### Brochures

[Wiring Devices Buyer's Guide](#)

### Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

### Specifications and datasheets

[Eaton Specification Sheet - L630P](#)

Application

Industrial

Torque rating

20 lbf-inch



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)