



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LC2103NI In-Wall Remote RF Dimmer, Nickel

Pass & Seymour/Legrand

Catalog Number	LC2103NI
Manufacturer	Pass & Seymour/Legrand
Description	Radiant™ RF Dimmer Aux, 2-Wire, Nickel
Weight per unit	0.3100 (lbs/each)
Product Category	Fan Speed Switches & Controls

Features

Load Rating	1500 (max)
Material	High Impact Plastic (MTL Polycarbonate Lexan)
package size	Unit: 4.8 x 3.03 x 2.48 (122 x 77 x 63): Master Case (Qty 20): 35 x 17 x 25 (889 x 431.8 x 635)
supply voltage	120

Material, Color, and Finish

Color	Nickel
-------	--------

Dimensions and Weight

Size	4.185 x 2.4 x 1.787
------	---------------------

Descriptions

Description	IN-WALL REMOTE RF DIMMER, NICKEL
extra long description	OnQ LC2103NI RADIANT RF DIMMER REMO
Long Description	radiant™ RF Dimmer Aux, 2-wire, Nickel
Product Type	Radiant RF Dimmer Remote Ni
Special Features	Remote dimmer, remote, Intuity Home Intelligence

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00804428032779
Manufacturers Part Number	LC2103NI
sub brand	Legrand-On-Q
UPC	804428032779

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Universal Lighting Control, 3-way switch

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	0.31



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Residential
environmental conditions	10 to 80 (relative humidity, non-condensing)
Frequency Rating	900
Mounting	Mounts in a standard electrical box
Operating Temperature	32 to 104 (0 to 43)
standard	UL, FCC, cULus, RoHS