

Pneumatic Crimping Tool - Pico Series 400

The Pico Series 400 is a versatile pneumatic crimping tool designed to work with various applications, including pin and socket contacts, solder-less terminals, and a variety of custom-specific applications. Critical parts are manufactured with high-strength S-7 tool steel, ensuring lightweight and durability. Production-ready tools are widely used in aerospace, defense, transportation, and energy fields.



Key Features

Benefits

Innovative Design	Lightweight and portable ideal for shop and field environments
Reduced process time	Pin and Sockets, Solderless Terminals, Ferrules and, many Custom Applications
Crimp Styles	Crimps No. 28 thru 2/0
Low-Maintenance	No operator adjustments required
Die-Set Selection	Interchangeable, Nonadjustable Die Heads ensuring quick setups between applications
Standards	MIL-C 22520/23-01

Pneumatic Crimping Tool - Pico Series 500

The Pico Series 500 is a versatile pneumatic crimping tool designed to work with various applications, including pin and socket contacts, solder-less terminals, and a variety of custom-specific applications. Critical parts are manufactured with high-strength S-7 tool steel, ensuring lightweight and durability. Production-ready tools are widely used in aerospace, defense, transportation, and energy fields.



Key Features

Benefits

Innovative Design	Lightweight and portable ideal for shop and field environments
Reduced process time	Pin and Sockets, Solderless Terminals, Ferrules and, many Custom Applications
Crimp Styles	Crimps No. 22 thru 250
Low-Maintenance	No operator adjustments required
Die-Set Selection	Interchangeable, Nonadjustable Die Heads ensuring quick setups between applications
Standards	MIL-C 22520/23-01

Power Connector Selection

	Product Families	Standard Barrel	Long Barrel	Short Barrel	Standard Tongue	Narrow Tongue	Inspection Window	No Inspection Window	Code Cable	Flex Cable
One Hole Lug AWG	A-Series	✓			✓			✓		✓
	LCA	✓			✓		✓		✓	
	LCAX	✓			✓		✓			✓
	S-R	✓			✓		✓		✓	
	LCAN	✓				✓	✓		✓	
	LCB			✓		✓		✓	✓	
	LCBX			✓		✓		✓	✓	✓
	LCAS			✓	✓		✓		✓	
Two Hole Lug AWG	LCD	✓			✓		✓		✓	
	LCDN	✓				✓	✓		✓	
	LCDX	✓			✓		✓		✓	✓
	LCDXN	✓			✓		✓		✓	✓
	LCCX			✓	✓		✓		✓	✓
	LCCXF			✓	✓		✓		✓	✓

Note: LCAX, LCDX, LCDXN, LCBX, LCCX, and LCCXF - AWG 1, 1/0, 2/0 & 250 are currently in development and not available at this time with Pico tooling.



One Hole Lug



Two Hole Lug



Standard Tongue



Narrow Tongue



Standard Barrel



Long Barrel



Inspection Window



No Inspection Window

Rennsteig Tools, Inc
805-388-5510
Rennsteig.us

PANDUIT[®]

© 2021 Panduit Corp.
ALL RIGHTS RESERVED.
Product Bulletin Number
PCCB16--WW-ENG
3/2021